# **DLRO 10 and DLRO 10X Digital Microhmmeter**



- Auto current reversal cancels standing emfs
- Protected to 600 V
- Automatically detects continuity in potential and current connections
- Multiple operating modes including fully automatic
- Alpha-numeric keypad for entering test notes (DLRO 10X)
- User selectable high and low limits (DLRO 10X)
- Printer output and memory (DLRO 10X)

## **DESCRIPTION**

DLRO 10 and DLRO 10X set the standards for low resistance measurement. DLRO 10 and DLRO 10X are fully automatic instruments, selecting the most suitable test current up to 10A d.c. to measure resistance from 0.1  $\mu\Omega$  to 2000  $\Omega$ , on one of seven ranges.

For users who desire more control over the measurement process, DLRO 10X uses a menu system controlled by a two-axis paddle to allow the user to manually select the maximum test current.

DLRO 10X also adds real time download of results and on board storage for later download to a PC.

Both instruments are built into a strong, lightweight case that is equally at home in the field or in the laboratory. Light enough to be worn around the neck, they are small enough to be taken into areas that were previously too small to access.

DLRO 10 uses a large, bright 4 1/2 -digit LED display while DLRO 10X has a large, backlit LCD display. Normally, measurements are made with forward and reverse currents to cancel the effects of any standing voltages across the test sample.

The average value is then displayed within 3 seconds, to a basic accuracy of 0.2%. DLRO 10X displays both forward and reverse measurements as well as the average of the two.

DLRO 10X allows the user to set high and low pass limits, thereby enabling simple go-no-go testing.

At the end of a test DLRO10X will store the test results, as well as any notes relevant to the test.

To assist operator safety and ease of use, both instruments are supplied complete with a pair of duplex handspikes with 1.2 m (4 ft) leads. One of the probes is fitted with LED's, which duplicate indicators on the instrument display indicating that all four contacts have been made, the presence of a high voltage across the load, and the presence of current flow while a load is discharging. A full range of test leads is available with probes, clamps and Kelvin clips.

Nickel Metal Hydride (NiMH) batteries power the instruments. The battery packs are interchange-able so that an exhausted battery may be recharged using the external charger supplied while testing continues using a spare pack. Although full charging will take 4 hours, a fast charge mode allows the battery to be 90% charged within 2 1/2 hours from a 12 volt battery or from a standard 120/230 V AC supply via the supplied charger. The battery pack contains its own battery state indicator, which allows the charge-state to be monitored, even without being connected to the instrument.

DLRO 10X is fitted with RS232 communications that will allow results to be downloaded in real time or stored for later retrieval.

Up to 700 sets of results may be stored within DLRO 10X complete with notes containing up to 200 characters which may be added using the on board keypad. These results can also be downloaded to a PC.

## **MEASUREMENT MODES:**

A variety of measurement modes are available. Since the introduction of V2.0 firmware, Normal, Auto, Continuous and Inductive mode are available on both the DLRO 10 and the DLRO  $10\mathrm{X}$ 

# Digital Microhmmeter

Megger.

DLRO 10 will display the average of the measurements achieved using forward and reverse current, while DLRO 10X displays both individual measurements and the average.

**Normal mode** initiates a test by pressing the Test button on the instrument front panel after connecting the test leads. Continuity of all four connections is checked, forward and reverse currents are applied.

**Auto mode** allows forward and reverse current measurements to be made and the average displayed simply by making contact with all four probes. This mode is ideal when working with the supplied handspikes. Each time the probes are removed and reconnected to the load another test will be performed without the need to press the test button on the instrument.

**Continuous mode** allows repeated measurements to be made on the same sample. Simply connect the test leads and press the test button. The measurement is updated every 3 seconds until the circuit is broken.

**Inductive mode** is intended for use when measuring inductive loads. When measuring inductive loads it is necessary to wait for the voltage to stabilise. This means that the measurement could take a few seconds or several minutes. The test leads are firmly connected to the item to be measured and the Test button is pressed. The instrument will pass a current through the sample and wait for the voltage to stabilise. If possible the current will be increased. This procedure will be repeated until the voltage detected falls into the range 15 mV to 200 mV. The instrument will then continue to take readings, which will gradually decrease to the true value as the voltage stabilises further. The operator decides when the result is stable and presses the Test button to terminate the test. Measurement is made with forward current only.

**Unidirectional mode**, on DLRO 10X only, applies a current in one direction only. This does not enable any standing emfs to be negated but speeds up the measurement process. Test starts automatically when probes are connected.

#### **APPLICATIONS**

The needs for accurate low resistance measurement are well known and very diverse. They range through Goods Receiving inspection of components to ground bonding and welded joints. Typical applications include, but are not limited to, making d.c. resistance measurements of:

- Switch and contact breaker resistance
- Busbar and cable joints
- Aircraft frame bonds and static control circuits
- Integrity of welded joints
- Inter-cell connections on battery systems up to 600 V peak
- Quality control of resistive components
- Transformer and motor winding resistance
- Rail and pipe bonds
- Metal alloys, welds and fuse resistance
- Graphite electrodes and other composites
- Wire and cable resistance
- Transmitter aerial and lightning conductor bonding

### **FEATURES AND BENEFITS**

- Small, lightweight and portable can be used in tight places, reduces the need for extra long leads and two person operation.
- Four terminal resistance method shows the true resistance of the item under test.
- Bright LED (DLRO 10) and LCD (DLRO 10X) displays are easily visible under all lighting conditions and reduce human error.
- Automatically applies forward and reverse currents which cancel out any standing voltages across the sample under test.
- Checks for undue noise during measurement, reducing the possibility of recording the incorrect result.
- Automatically detects continuity in P and C circuits, preventing erroneously high reading to be taken due to high resistance contact
- Battery module has a battery condition indicator allowing the user to check the state of spare batteries without connecting to the instrument.
- RS232 connector on the DLRO 10X allows downloading of results in real time or stored for later retrieval.



The DLROs are light enough to be worn around the neck. They are also small enough to be taken into areas which were previously too cramped for easy testing.



				Full Scale Volts		Test Current	
Full Scale	Resolution	Accuracy*	Resistive	Inductive	Resistive	Inductive	
1.9999 m <b>Ω</b>	$0.1 \mu\Omega$	$\pm 0.2\% \pm 0.2\mu\Omega$	20 mV	n/a	10 A	n/a	
19.999 mΩ	$1 \mu\Omega$	$\pm 0.2\% \pm 2 \mu\Omega$	20 mV	20 mV	1 A	1 A	
199.99 mΩ	$10 \mu\Omega$	$\pm 0.2\% \pm 20 \mu\Omega$	20 mV	200 mV	100 mA	1 A	
1.9999 Ω	$100  \mu\Omega$	$\pm 0.2\% \pm 0.2 \text{ m}$ Ω	20 mV	200 mV	10 mA	100 mA	
19.999 Ω	$1~\text{m}\Omega$	$\pm 0.2\% \pm 2 \text{ m}\Omega$	20 mV	200 mV	1 mA	10 mA	
199.99 Ω	$10~\mathrm{m}\Omega$	$\pm 0.2\% \pm 20 \text{ m}\Omega$	20 mV	200 mV	100 μΑ	1 mA	
1999.9 Ω	$100~\mathrm{m}\Omega$	±0.2% ±0.2 Ω	200 mV	200 mV	100 μΑ	$100 \mu A$	

	DLRO 10	DLRO 10X			
Measurement: Mode:	Manual, Auto, Continuous,	Manual, Auto, Continuous,			
	High Power	High Power, Unidirectional			
Control:	Fully Automatic Fully Automatic/Manual				
Speed:	<3s for forward & reverse current and to display average				
Display: Measurement:	41/2 digit seven segment LED				
Range and Safety:	LED indication	Large backlit LCD			
Test Method:	Single cycle reversing d.c. ratiometric measurement -average result display.				
Test Current: Accuracy:	±10%				
Stability:	<10 ppm per second				
Maximum Lead Resistance:	$100 \text{ m}\Omega$ total for 10A operation irrespective of battery condition.				
Voltmeter input impedance:	> 200 kΩ				
Hum rejection:	Less than $1\% \pm 20$ digits additional error with $100$ mV peak $50/60$ Hz. on the potential leads. Warning will show if hum or noise exceeds this level.				
Data: Transfer:		Real Time or from storage via RS232			
Storage:		700 tests			
Memo Field		Up to 200 characters per test via integral alphanumeric keypad			
Battery: Capacity:	7 Ah NiMH rechargeable				
Life:	Typically 1000 x 10 A tests before recharge				
Recharge:	Via External 90V - 260V 50/60 Hz charger or from 12 to 15V d.c. supply				
Charging Rate: Standard:	2.5 hours to 90% capacity, 4 hrs for full charge				
<b>Temperature:</b> Operation:	+5°C to +45°C (41°F to 113°F) at full specification				
	-10°C to +50°C (14°F to 122°F) at reduced accuracy				
Storage	-30°C to +70°C (-22°F to 158°F)				
Co-efficient:	<0.01% per °C over range 5°C to 40°C (<0.006% per °F from 41°F to 104°F)				
Slow charging:	+10°C to +45°C (50°F to 113°F)				
Humidity (max):	90% RH @ 40°C (104°F) non-condensing				
Altitude (max):	2000m (6562 ft) to full safety specifications				
Safety:	In accordance with IEC61010-1 600V Category III - only when DH6 leads are used				
EMC:	In accordance with IEC61326-1				
	220 x 100 x 237 mm (8.6 x 4 x 9.5 in)				
Dimensions: Weight:	220 x 100 x 23/ IIIII (0.0 x 4 x 7.7 III)				

<sup>\*</sup> The accuracy stated assumes forward and reverse measurements.

Inductive mode or undirectional mode will introduce an undefined error if an external EMF is present.

Item (Qty)	Order No.	Item (Qty)		Order No
DLRO 10 Digital Low Resistance Ohmm	eter 6111-	Straight Duplex Handspikes (2)		
DLRO10X Digital Low Resistance Ohmr	neter 6111-	Heavy Duty with fixed contacts.	2m/7ft	242002-7
Complete with			5.5m/18ft	242002-18
7 Ah NiMH battery module.	6340-	1	9m/30ft	242002-30
DH4 Duplex handspikes (2),		Duplex Heavy Duty 5cm (2")		
one with indicator lights. 1.2m / 4 ft	6111-	3 C-Clamps. (2)	2m/7ft	242004-7
Battery charger for operation from 115	5/230 V		5.5m/18ft	242004-1
50/60Hz supply.	6280-	3	9m/30ft	242004-30
Cigar lighter adapter for battery charg	ing. 6280-	2 Duplex handspikes with replace	able	
User guide.	6172-	Needle Points	2m/7ft	242003-7
Warranty book.	6170-	B Duplex 1.27 cm (1/2 ")		
Optional Accessories at extra cost		Kelvin Clips. (2) gold plated	2m/7ft	241005-7
Carrying case for DLRO10/10X		silver plated	2m/7ft	242005-7
and all standard accessories.	6380-	B Duplex 3.8 cm (11/2")		
Carrying case for optional lead sets.	18:	B Kelvin Clips. (2)	2m/7ft	242006-
Calibration Shunt,10 Ω, current rating	1 mA. 249	)	5.5m/18ft	242006-18
Calibration Shunt, 1 $\Omega$ , current rating 1	10 mA. 249	1	9m/30ft	242006-30
Calibration Shunt, 100 mΩ current rati	ng 1A. 249	Single Leads		
Calibration Shunt, 10 mΩ current ratin	g 10 A. 249	Single handspike (1) for		
Certificate of Calibration for Shunts, N	IST CERT-N	Γ potential measurement.	2m/7ft	242021-7
Replacement tips for DH4, DH5 and DH	16 handspikes.		5.5m/18ft	242021-18
Needle point	25940-	2	9m/30ft	242021-30
Serrated end	25940-	Current clip (1) for current		
Optional Test Leads at extra cost		connections.	2m/7ft	242041-7
Duplex Leads			5.5m/18ft	242041-18
DH5 straight duplex handspikes (2).			9m/30ft	242041-30
One has indicator lights. 2.5	m/8ft 6111-	7		
DH6 Duplex handspikes (2) suitable		-		
for working on 600 V. systems. 2.5	m/8ft 6111-	3		
Duplex Handspikes (2) with spring		-		
	/7ft 24201	7		
2.5	m/8ft 6111-	2		
5.5	m/18ft 242011	3		
only 1 lead supplied 6m	/20ft 6111-	3		
	/30ft 242011	)		